


mounting rail SLZS-40- -

Part number: 150919

FESTO

Overall rail length is 230 mm plus stroke.



Data sheet

Feature	Value
Design	T-slot for proximity sensor
Max. profile length	2,800 mm
Assembly position	Any
Design structure	Sensor strip
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 60 °C
Mounting type	With through-hole and screw
Material of profile	Wrought Aluminium alloy Anodised
Materials note	Conforms to RoHS
Material screws	High alloy steel