


one-way flow control valve GRLA-1/4-NPT-B

Part number: 151547

FESTO



Data sheet

Feature	Value
Valve function	One-way flow control function for exhaust air
Pneumatic connection, port 1	Female thread 1/4 NPT
Pneumatic connection, port 2	Male thread 1/4 NPT
Adjusting element	Slotted head screw
Mounting type	Threaded
Standard nominal flow rate in flow control direction	610 l/min
Standard nominal flow rate in non-return direction	450 ... 820 l/min
Ambient temperature	-10 ... 60 °C
Assembly position	Any
Operating pressure complete temperature range	0.3 ... 10 bar
Standard flow rate in flow control direction 0.6->0 MPa (6->0 bar, 87->0 psi)	1,200 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Medium temperature	-10 ... 60 °C
Nominal size	6 mm
Max. tightening torque	11 Nm
Material of threaded plug	Wrought Aluminium alloy
Materials note	Conforms to RoHS
Material seals	NBR
Material adjusting screw	Brass
Material swivel fitting	Zinc die-casting