


non-return valve
HA-1/8-QS-6

Part number: 153448



Flow rate from the male thread to the QS plug connector.
This type is suitable for vacuum.



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	R1/8
Pneumatic connection, port 2	QS-6
Mounting type	Threaded
Standard nominal flow rate	311 l/min
Operating pressure	-1 ... 10 bar
Ambient temperature	0 ... 60 °C
Material housing	Nickel-plated brass
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Product weight	11 g
Materials note	Conforms to RoHS