## pressure regulator LRMA-1/4-QS-6 Part number: 153492 Product to be discontinued

With pressure gauge.

Type to be discontinued. Available until 2021. See Support Portal for alternative products.





**FESTO** 

## **Data sheet**

Feature	Value
Controller function	Output pressure constant
	with secondary exhaust
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	QS-6
Mounting type	with through hole
Standard nominal flow rate	96 l/min
Inlet pressure 1	0 9 bar
Ambient temperature	0 60 °C
Material housing	PBT-reinforced
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Actuator lock	Knurled screw with lock nut
Assembly position	Any
Design structure	directly-controlled piston regulator
	with looped-through compressed air supply
Pressure gauge	with pressure gauge
Pressure regulation range	1 8 bar
Product weight	55 g
Material of threaded plug	Brass
	Nickel plated
Material of threaded seal	PTFE