
## pressure regulator LR-QS-4 Part number: 153540 Product to be discontinued

Type to be discontinued. Available until 2021. See Support Portal for alternative products.







## **Data sheet**

| Feature                      | Value  |
|------------------------------|--|
| Controller function          | Output pressure constant                                 |
|                              | with secondary exhaust                                   |
| Pneumatic connection, port 1 | QS-4   |
| Pneumatic connection, port 2 | QS-4   |
| Mounting type                | with through hole  |
| Standard nominal flow rate   | 67 l/min   |
| Inlet pressure 1             | 0 9 bar  |
| Ambient temperature          | 0 60 °C  |
| Material housing             | PBT-reinforced   |
| Operating medium             | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Actuator lock                | Knurled screw with lock nut                              |
| Assembly position            | Any  |
| Design structure             | directly-controlled piston regulator                     |
|                              | with looped-through compressed air supply                |
| Pressure regulation range    | 1 8 bar  |
| Product weight               | 33 g   |
| Material of threaded plug    | Brass  |
|                              | Nickel plated  |
| Material of threaded seal    | PTFE   |