

# Push-in bulkhead connector QSS-1/4T-U

Part number: 153763

FESTO

This product is only available if ordered from the Festo Corporation, USA.  
Products to be discontinued. Available until 2011.



## Data sheet

| Feature                                  | Value                             |
|--|-----------------------------------|
| Size                                     | Standard                          |
| Nominal size                             | 4 mm                              |
| Assembly position                        | Any                               |
| Container size                           | 1                                 |
| Design structure                         | Push/pull principle               |
| Operating pressure                       | -0.95 ... 10 bar                  |
| Temperature dependent operating pressure | -0.95 ... 10 bar                  |
| Operating medium                         | Filtered compressed air<br>Vacuum |
| Corrosion resistance classification CRC  | 1                                 |
| Ambient temperature                      | -10 ... 60 °C                     |
| Authorisation                            | Germanischer Lloyd                |
| Pneumatic connection                     | for tubing, 1/4" outside diameter |
| Colour of release ring                   | Grey                              |
| Materials note                           | Conforms to RoHS                  |
| Materials information, housing           | Brass<br>Nickel plated            |
| Release ring material data               | POM                               |
| Materials information for tubing seal    | NBR                               |
| Hose clamping segment material data      | High alloy steel, non-corrosive   |