

Push-in T connector QST3-5/16T-3/16-U


Part number: 153806

FESTO

Rotatable 360°, 4 outlets.

This product is only available if ordered from the Festo Corporation, USA.

Products to be discontinued. Available until 2011.



Data sheet

Feature	Value
Size	Standard
Assembly position	Any
Design structure	Push/pull principle
Container size	1
Operating pressure	-0.95 ... 10 bar
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Filtered compressed air Vacuum
Corrosion resistance classification CRC	1
Ambient temperature	-10 ... 60 °C
Authorisation	Germanischer Lloyd
Product weight	23 g
Number of outputs	4
Number of supply lines	1
Pneumatic connection, supply line	for tubing, 5/16" outside diameter
Pneumatic connection, output	for tubing, 3/16" outside diameter for tubing, 5/16" outside diameter
Colour of release ring	Grey
Materials note	Conforms to RoHS
Materials information, housing	PBT
Release ring material data	POM
Materials information for tubing seal	NBR
Hose clamping segment material data	High alloy steel, non-corrosive