



CRQH-DR-3/4-B

Ball valve drive unit

Feature	Data/description
Nominal size	20 mm
Type of actuation	manual
Sealing principle	soft
Design structure	Ball valve
Valve function	2/2 Bistable
Operating pressure	0 - 63 bar
Standard nominal flow rate	28.600 l/min
Operating medium	Water Neutral gases Compressed air
Medium temperature	-40 - 200 °C
Ambient temperature	-40 - 230 °C
Product weight	1.700 g
Mounting type	Line installation
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 2	G3/4
Materials note	Contains PWIS substances
Materials information for cover	Stainless steel casting
Materials information for seals	FPM PTFE
Materials information, housing	Stainless steel casting