

barbed hose fitting N-1/8-P-6-MS

Part number: 15630

FESTO

Brass version



Data sheet

Feature	Value
Nominal size	4.5 mm
Type of seal on screw-in stud	Sealing ring
Assembly position	Any
Design	Straight design
Container size	10
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Max. tightening torque	5 Nm
Product weight	9 g
Pneumatic connection, port 1	Male thread G1/8
Pneumatic connection, port 2	For tubing internal diameter 6 mm
Materials note	Conforms to RoHS
Material housing	Brass