


reset module PZVT-AUT

Part number: 158496

FESTO



Data sheet

Feature	Value
Design structure	mechanical sequence counter with pneumatic drive
Switch-off pressure	≤ 0.1 bar
Operating pressure	2 ... 6 bar
Switch-on pressure	≥ 1.6 bar
Standard nominal flow rate	50 l/min
Adjustable delay times	0.2 ... 2 s
Pause period for reset	≥ 200 ms
Repetition accuracy, time setting	$\pm 0,3$ s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP54 With protective cover and panel frame to IEC 60529
Ambient temperature	-15 ... 60 °C
Product weight	50 g
Mounting type	Front panel installation
Pneumatic connection	Female thread M5
Materials note	Conforms to RoHS
Material housing	ABS