

LFMP-3/8-S-C

Fine filter cartridge

Data sheet

Part no.: 159174

Page:1

Feature	Data/description
Design of filter	Fibre
Modular design	Yes
Series	S
Input pressure 1 max. (bar)	16 bar
Output pressure 2 min.	0,4 bar
Minimum medium temperature	1,5 °C
Maximum medium temperature	60 °C
Grade of filtration	0,01 µm
Material of filter	Boron silicate fibre
Standard nominal flow rate 1-2	330 l/min
Operating medium input I	Compressed air, filtered 5 µm