

**LFMP-1/2-S-C**

Micro filter cartridge

Data sheet

Part no.: 159175

Page:1

<b>Feature</b>	<b>Data/description</b>
Design of filter	<b>Fibre</b>
Modular design	<b>Yes</b>
Series	<b>S</b>
Input pressure 1 max. (bar)	<b>16 bar</b>
Output pressure 2 min.	<b>0,4 bar</b>
Minimum medium temperature	<b>1,5 °C</b>
Maximum medium temperature	<b>60 °C</b>
Grade of filtration	<b>0,01 um</b>
Material of filter	<b>Boron silicate fibre</b>
Standard nominal flow rate 1-2	<b>600 l/min</b>
Operating medium input I	<b>Compressed air, filtered 5 µm</b>