

Suction cup VAS-125-3/8-SI

Part number: 160991

FESTO

Sealing ring is not included in the scope of delivery.
Type to be discontinued. Available until 2012.



Data sheet

Feature	Value
Nominal size	7 mm
suction cup diameter	125 mm
Effective suction diameter	105 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-40 ... 200 °C
Breakaway force at 70% vacuum	606 N
Product weight	148 g
Mounting thread	G3/8
suction cup mounting	G3/8
Vacuum connection	G3/8
Shore hardness	60 +/- 5
Materials information for screw-in stud	Wrought Aluminium alloy
Materials note	Contains PWIS substances
Materials information for suction cup	VMQ (silicon)