


clevis foot CRLNG-40

Part number: 161841

FESTO

Corrosion resistant,
for cylinders CRDNGS.



Data sheet

Feature	Value
Size	40
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Assembly position	Any
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
Ambient temperature	-40 ... 80 °C
Product weight	161 g
Materials note	Conforms to RoHS
Material mounting	electrolytically polished High alloy steel
Material bearing	Plastic