

# Sub-base PAML-CP-186-HP3-G14

Part number: 1629300

FESTO



## Data sheet

Feature	Value
Size	186
Nominal size DN	54
Series	L
Operating pressure	0 MPa...0 MPa 0 bar...0 bar
Operating medium	Compressed air to ISO 8573-1:2010 [---]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...10 °C
Suitable for use with food	See supplementary material information
Media temperature	5 °C...5 °C
Ambient temperature	5 °C...5 °C
Product weight	4700 g...4700 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Note on materials	RoHS-compliant
Material sub-base	Wrought aluminium alloy
Material seals	NBR
Material screws	Stainless steel