

**PAN-L-10x1,5-NT****Plastic tubing**

<b>Feature</b>	<b>Data/description</b>
Ambient temperature	-30 - 80 °C
Operating medium	Filtered compressed air Vacuum
Shore hardness	55 +/- 3
Colour	neutral
Inside diameter	7,000 mm
Outside diameter	10,000 mm
Food-industry approval	90/128/EWG
Materials note	Copper and PTFE-free
Product weight according to length	0,0420 kg/m
Min. bending radius	58,000 mm
Materials information for tubing	TPE-A