

PAN-L-16x2-NT**Plastic tubing**

Feature	Data/description
Ambient temperature	-35 - 80 °C
Operating medium	Filtered compressed air Vacuum
Shore hardness	55 +/- 3
Colour	neutral
Inside diameter	12,000 mm
Outside diameter	16,000 mm
Food-industry approval	90/128/EWG
Materials note	Copper and PTFE-free
Product weight according to length	0,0920 kg/m
Min. bending radius	94,000 mm
Materials information for tubing	TPE-A