

**CPV18-EPR-PE**

End plate

Data sheet

Part no.: 163195

Page:1

<b>Feature</b>	<b>Data/description</b>
Type of mounting sub-base	<b>Screw</b>
Operating pressure min.	<b>-0,9 bar</b>
Operating pressure max.	<b>16 bar</b>
Minimum ambient temperature	<b>-10 °C</b>
Maximum ambient temperature	<b>50 °C</b>
Minimum medium temperature	<b>-10 °C</b>
Maximum medium temperature	<b>50 °C</b>
CT criterion	<b>Free of copper and PTFE</b>
Medium	<b>Dried filtered compressed air (may be lubricated)</b>