

CPV18-EPR-E

End plate

Data sheet

Part no.: 163197

Page:1

Feature	Data/description
Type of mounting sub-base	Screw
Operating pressure min.	-0,9 bar
Operating pressure max.	16 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	50 °C
Air connection type connection 1	Thread
Air connection type connections 3,5	Thread
Air connection type connections 12,14	Thread
Air connection type connections 82,84	Thread
Air connection type connection 11	Thread
Thread for port 1	G 3/8
Thread for ports 3, 5	G 1/2
Thread for ports 12, 14	G 1/4
Thread for ports 82, 84	G 1/4
Thread for port 11	G 3/8
CT criterion	Free of copper and PTFE
Medium	Dried filtered compressed air (may be lubricated)