

## CPV18-EPR-G

End plate

Data sheet

Part no.: 163199

Page:1

Feature	Data/description
Type of mounting sub-base	<b>Screw</b>
Operating pressure min.	<b>-0,9 bar</b>
Operating pressure max.	<b>16 bar</b>
Minimum ambient temperature	<b>-10 °C</b>
Maximum ambient temperature	<b>50 °C</b>
Minimum medium temperature	<b>-10 °C</b>
Maximum medium temperature	<b>50 °C</b>
Air connection type connection 1	<b>Thread</b>
Air connection type connections 3,5	<b>Thread</b>
Air connection type connections 12,14	<b>Thread</b>
Air connection type connections 82,84	<b>Thread</b>
Air connection type connection 11	<b>Thread</b>
Thread for port 1	<b>G 3/8</b>
Thread for ports 3, 5	<b>G 1/2</b>
Thread for ports 12, 14	<b>G 1/4</b>
Thread for ports 82, 84	<b>G 1/4</b>
Thread for port 11	<b>G 3/8</b>
CT criterion	<b>Free of copper and PTFE</b>
Medium	<b>Dried filtered compressed air (may be lubricated)</b>