

CPV18-EPR

End plate

Data sheet

Part no.: 163281

Page:1

Feature	Data/description
Type of mounting sub-base	Screw
Operating pressure min.	-0,9 bar
Operating pressure max.	16 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	50 °C
CT criterion	Free of copper and PTFE
Medium	Dried filtered compressed air (may be lubricated)