



QH-DR-1 1/2-B

Ball valve drive unit

Feature	Data/description
Nominal size	40 mm
Type of actuation	manual
Sealing principle	soft
Design structure	Ball valve
Valve function	2/2 Bistable
Operating pressure	<= 40 bar
Standard nominal flow rate	159.500 l/min
Operating medium	Water Neutral gases Compressed air
Medium temperature	-40 - 200 °C
Ambient temperature	-20 - 85 °C
Product weight	4.650 g
Mounting type	Line installation
Pneumatic connection, port 1	G1 1/2
Pneumatic connection, port 2	G1 1/2
Materials note	Contains PWIS substances
Materials information for cover	Brass
Materials information for seals	FPM PTFE
Materials information, housing	Brass