



LFR-1/4-D-O-MINI-A-CT

Filter regulator

Feature	Data/description
Size	Mini
Series	D
Actuator lock	Rotary knob with lock
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Filter regulator without pressure gauge
Max. condensate volume	22 cm ³
Bowl guard	Metal bowl guard
Pressure gauge	G1/8" prepared
Pressure control range	0,5 - 12 bar
Inlet pressure 1	1,5 - 12 bar
Max. pressure hysteresis	0,3 bar
Standard nominal flow rate	1.400 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Product weight	410 g
Mounting type	with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances Copper and PTFE-free
Materials information, housing	Zinc die-casting



Data sheet

Part no.: **165788**

Page:2

LFR-1/4-D-O-MINI-A-CT**Filter regulator**

Feature	Data/description
Materials information for bowl	PC