


Double DNGU-32-50PPV-A-CT

Part number: 166090

FESTO



Datasheet

Feature	Value
Mode of operation	Double acting
Type of mounting	Screw
Form, external	Profile
Form piston	Round
Form piston rod	Round
In accordance with standard ISO	ISO 6431
In accordance with standard VDMA	VDMA 24562
Sensing type	Magnetic
Type of cushioning	Adjustable pneumatic cushioning
Cushioning length	19 mm
Protection against torsion	None
Piston, nominal size	32 mm
Stroke	50 mm
Piston rod diameter	12 mm
Thread type (piston rod) (KK)	M
Thread diameter (metric)	10 mm
Pitch	1,25 mm
Thread length (piston rod)	22 mm
Overall length	196 mm
Operating pressure min.	0,6 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-20 °C
Maximum ambient temperature	80 °C
Connection type bearing cap (EE)	Female thread
Thread type (bearing cap)	G
Thread diameter (inch)	1/8 inch
Silicone status	Free
CT criterion	CT-free
Connection type cover cap	Thread
Thread type (cover cap)	G
Thread diameter (inch)	1/8 inch
Effective force (theor.) at 6 bar, adv	.483 N
Effect. force (theor.) at 6 bar, retur	n415 N

Feature	Value
Lateral force	58 N
Bending load	750 N
Air consumption at 6 bar, advance	0,28 L/<-->
Air consumption at 6 bar, return	0,24 L/<-->