



Double DNGU-80-200PPV-A-CT

Part number: 166135

FESTO



Datasheet

| Feature | Value |
|--|---------------------------------|
| Mode of operation | Double acting |
| Type of mounting | Screw |
| Form, external | Profile |
| Form piston | Round |
| Form piston rod | Round |
| In accordance with standard ISO | ISO 6431 |
| In accordance with standard VDMA | VDMA 24562 |
| Sensing type | Magnetic |
| Type of cushioning | Adjustable pneumatic cushioning |
| Cushioning length | 30 mm |
| Protection against torsion | None |
| Piston, nominal size | 80 mm |
| Stroke | 200 mm |
| Piston rod diameter | 25 mm |
| Thread type (piston rod) (KK) | M |
| Thread diameter (metric) | 20 mm |
| Pitch | 1,5 mm |
| Thread length (piston rod) | 40 mm |
| Overall length | 418 mm |
| Operating pressure min. | 0,6 bar |
| Operating pressure max. | 10 bar |
| Minimum ambient temperature | -20 Cel |
| Maximum ambient temperature | 80 Cel |
| Connection type bearing cap (EE) | Thread |
| Thread type (bearing cap) | G |
| Thread diameter (inch) | 3/8 inch |
| Silicone status | Free |
| CT criterion | CT-free |
| Connection type cover cap | Thread |
| Thread type (cover cap) | G |
| Thread diameter (inch) | 3/8 inch |
| Effective force (theor.) at 6 bar, adv | .3016 N |
| Effect. force (theor.) at 6 bar, retur | n2721 N |

| Feature | Value |
|-----------------------------------|--------------|
| Lateral force | 240 N |
| Maximum buckling load | 50000 N |
| Bending load | 1500 N |
| Air consumption at 6 bar, advance | 7,04 l/<--> |
| Air consumption at 6 bar, return | 6,34 l/<--> |