

Heavy-duty guide HD-18- -

Part number: 170025


FESTO

Configurable

To configure first add product to the basket.

Depending on configuration, the technical data given on the data sheet and the relevant accessories might not match exactly for this product.

Products to be discontinued. Available until 2009.



Exemplary representation

Data sheet

~ConfIndependentDatasheet

Feature	Value
Size	18
Stroke	10 ... 1,810 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide axis without drive unit
Max. speed	3 m/s
Corrosion resistance classification CRC	0
Ambient temperature	-10 ... 60 °C
Max. force Fy	1,820 N
Max. force Fz	1,820 N
Max. torque Mx	70 Nm
Max. torque My	115 Nm
Max. torque Mz	112 Nm
Moving mass	450 g
Moving mass with 0 mm stroke	450 g
Additional weight per 10 mm stroke	72 g
Basic weight for 0 mm stroke	2,950 g
Materials information for guide component	Steel
Materials information, housing	Wrought Aluminium alloy Anodised