

## SPC-FIO-2E/2A-M8

### I/O module

Feature	Data/description
Fuse protection, output	Electronic Via sum of all outputs Max. tripping current: 500 mA
Fuse protection for sensor supply voltage	Electronic
Number of digital outputs	2
Number of digital inputs	2
Type of outputs	Per IEC 61131-2 Positive logic (PNP) No electrical isolation
Type of inputs	Per IEC 61131-2 Positive logic (PNP) No electrical isolation
Sensor supply	0.5 A from internal power supply
Supply power, outputs	24 V from SPC 200
Current-carrying capacity per output	250 mA
Typical current consumption, plug-in module	50 mA
Protection class	IP65 to IEC 60529
Ambient temperature	0 - 50 °C
Product weight	266 g
Electrical connection, outputs	Plug socket Round design M8 3-pin
Electrical connection, inputs	Plug socket Round design M8 3-pin
Electrical connection, AIF IN	5-pin