

KVI-CP-2-GS-GD-5

Connecting cable

| Feature | Data/description |
|--------------------------------------|---------------------------------|
| Assembly position | Any |
| Operating voltage AC | <= 60 V |
| Permissible current load | 3 A |
| Protection class | IP65 |
| Ambient temperature | -5 - 80 °C -20 - 70 °C |
| Product weight | 262 g |
| Electrical connection | Plug straight / socket straight |
| Cable structure | 5 x 0,24 mm ² |
| Cable diameter | 5,2 mm |
| Cable length | 5 m |
| Mounting type | With sleeve nut |
| Materials information, housing | Brass Nickel plated |
| Materials information, cable sheaths | PUR |
| Materials information, plug | Bronze Gold plated |