

# Filter LF-3/8-D-5M-MINI-NPT

Part number: 173686

FESTO



## Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical
Grade of filtration	5 µm
Condensate drain	Manual, non-detenting
Max. condensate volume	22 cm <sup>3</sup>
Bowl guard	Metal bowl guard
Operating pressure	0 bar...16 bar
Standard nominal flow rate	1100 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Type of mounting	Either: In-line installation Via mounting bracket
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Note on materials	RoHS-compliant
Material filter	PE
Material housing	Die-cast zinc
Material bowl	PC