

# fine filter combination LFMBA-1/8-D-MINI-NPT



Part number: 173740

Classic - do not use for new projects

FESTO

Micro filter 1 µm for prefiltration and micro filter 0.01 µm, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



## Data sheet

Feature	Value
Size	Mini
Series	D
Assembly position	Vertical
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	manual momentary-contact
Bowl guard	Metal bowl guard
Operating pressure	1 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
PWIS conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2] Inert gases
Medium temperature	1.5 ... 60 °C
Residual oil content	0.01 mg/m <sup>3</sup>
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories
Pneumatic connection, port 1	1/8 NPT
Pneumatic connection, port 2	1/8 NPT
Materials note	Conforms to RoHS
Material filter	Boron silicate fibre
Material housing	Zinc die-casting
Material bowl	PC