

# Service unit FRC-3/8-D-MINI-A-NPT

Part number: 173845

FESTO



## Data sheet

Feature	Value
Size	Mini
Condensate drain	Fully automatic
Grade of filtration	40 µm
Operating pressure	2 bar...12 bar
Pressure regulation range	0.5 bar...12 bar
Standard nominal flow rate	1200 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:8:-] Inert gases
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	660 g
Type of mounting	With accessories
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Note on materials	RoHS-compliant
Material housing	Die-cast zinc
Material bowl	PC