


# plug SEA-M12-5GS-PG7

Part number: 175487

FESTO



## Data sheet

Feature	Value
Based on the standard	EN 61076-2-101 EN 61984
Mounting type	with threaded sleeve
Assembly position	Any
Product weight	21.5 g
Electrical connection	5-pin Plug pattern type A to EN 175301-803 M12X1 round plug connector Straight plug / screw terminal
Operating voltage range DC	$\leq 60$ V
Operating voltage range AC	$\leq 60$ V
Acceptable current load at 40°C	4 A
Surge strength	1.5 kV
Cable gland connection	Pg7
Permissible cable diameter	4 ... 6 mm
Terminal cross-section	0.75 mm <sup>2</sup>
Protection class	IP67
Ambient temperature	-40 ... 85 °C
CE mark (see declaration of conformity)	to EU directive low-voltage devices
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	1 - Low corrosion stress
Material housing	PBT
Housing colour	Black
Material of union nut	Zinc die-casting Nickel plated
Material electrical contact	Brass White bronze coated