

Valve kit CPV14-BS-5/3G-1/8

Part number: 176057

FESTO



Data sheet

Feature	Value
Valve function	5/3 closed
pneumatic working port	G1/8
Operating pressure	2.5 bar...10 bar
Nominal size	6 mm
Mounting position	optional
Burst pressure	30 bar
Switching time off	30 ms
Switching time on	22 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Shock resistance	30 g/11 ms to EN 60068-2-27
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	190 g
Type of mounting	With through-hole
Pneumatic connection, port 2	G1/8
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Die-cast zinc