

swivel flange SNCB-32-R3

Part number: 176944

FESTO



Data sheet

Feature	Value
Size	32
Based on the standard	ISO 15552
Variants	Excellent corrosion protection
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F5a
Ambient temperature	-40 ... 90 °C
Product weight	100 g
Materials note	Conforms to RoHS
Material mounting	Aluminium die cast With protective coating
Material mounting pin	High alloy steel, non-corrosive
Material bearing	Plastic
Material disc	steel, galvanized
Material screws	High alloy steel, non-corrosive
Material lock	Spring steel, galvanised