

connecting cable KEA-1-25P-5

Part number: 177413

FESTO



Data sheet

Feature	Value
Mounting type	with through hole
Product weight	2,040 g
Electrical connection	Plug socket Sub-D 25-pin
Operating voltage range DC	≤ 250 V
Operating voltage range AC	≤ 250 V
Permissible current load	4 A
Cable length	5 m
Cable diameter	12 mm
Cable structure	25x0,34
Protection class	IP65
Ambient temperature	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
Materials information, cable sheaths	PVC
Materials information, housing	PA
Material information for crimp connectors	Copper alloy Gold plated
Assembly position	Any