

Compressed-air PQ-VU-22X2X3000

Part number: 177739

FESTO

Datasheet

Feature	Value
Nominal size (metric)	22 mm
Internal diameter	18 mm
Outside diameter	22 mm
Wall thickness	2 mm
Operating pressure min.	-0,95 bar
Operating pressure max. at 20°C	15 bar
Operating pressure max. at 30°C	14 bar
Operating pressure max. at 40°C	12 bar
Operating pressure max. at 50°C	10 bar
Operating pressure max. at 60°C	9 bar
Operating pressure max. at 70°C	8 bar
Operating pressure max. at 75°C	7 bar
Suitable for vacuum	Yes
Minimum ambient temperature	-30 °C
Maximum ambient temperature	75 °C
Material designation	AlMgSi0,5
Material abbreviation	NL-AL
Material number	3.3206
Coating	Polyethylene
Silicone status	Free
Color definition	aterul
Color	black
Color code	black