



## LR-M3-G3/4-16GK Pressure regulator

Feature	Data/description
Size	3
Series	M
Actuator lock	Rotary knob with lock
Assembly position	Any
Design structure	directly-controlled diaphragm regulator
Controller function	with initial pressure compensation Output pressure constant
Pressure gauge	with pressure gauge
Pressure control range	0 - 16 bar
Inlet pressure 1	0 - 21 bar
Standard nominal flow rate	1.400 l/min
Operating medium	Filtered compressed air, 40 µm filtration
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	952 g
Mounting type	Front panel installation Line installation with accessories
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 2	G3/4
Materials note	Contains PWIS substances
Materials information for control panel	POM
Materials information for seals	NBR
Materials information, housing	Zinc die-casting



## LR-M3-G3/4-16GK

### Pressure regulator

Feature	Data/description
Materials information for membrane	NBR Brass