



LFR-M1-G1/8-C04UG

Filter regulator

Feature	Data/description
Size	1
Series	M
Actuator lock	Rotary knob with lock
Grade of filtration	5 µm
Condensate drain	fully automatic
Design structure	Filter regulator with pressure gauge
Max. condensate volume	10,25 cm ³
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Pressure control range	0 - 4 bar
Inlet pressure 1	0 - 17 bar
Max. pressure hysteresis	0,4 bar
Standard nominal flow rate	830 l/min
Operating medium	Compressed air
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	374 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting



Data sheet

Part no.: **179194**

Page:2

LFR-M1-G1/8-C04UG**Filter regulator**

Feature	Data/description
Materials information for bowl	Zinc die-casting