



LFR-M2-G1/2-C04RG

Filter regulator

Feature	Data/description
Size	2
Series	M
Actuator lock	Rotary knob with lock
Grade of filtration	5 µm
Condensate drain	manual rotary
Design structure	Filter regulator with pressure gauge
Max. condensate volume	52,75 cm ³
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Pressure control range	0 - 4 bar
Inlet pressure 1	0 - 12 bar
Standard nominal flow rate	5.900 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Product weight	848 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting
Materials information for bowl	PC