



LFR-M3-G3/4-C10T

Filter regulator

| Feature | Data/description |
|--------------------------------|---|
| Size | 3 |
| Series | M |
| Actuator lock | Rotary knob with lock |
| Grade of filtration | 5 µm |
| Condensate drain | manual rotary |
| Design structure | Filter regulator without pressure gauge |
| Max. condensate volume | 72,5 cm ³ |
| Bowl guard | Plastic guard |
| Pressure gauge | G1/4" prepared |
| Pressure control range | 0 - 10 bar |
| Inlet pressure 1 | 0 - 17 bar |
| Standard nominal flow rate | 3.000 l/min |
| Operating medium | Compressed air |
| Medium temperature | -10 - 80 °C |
| Ambient temperature | -10 - 80 °C |
| Product weight | 1.713 g |
| Mounting type | Optional Line installation with accessories |
| Pneumatic connection, port 1 | G3/4 |
| Pneumatic connection, port 2 | G3/4 |
| Materials note | Contains PWIS substances |
| Materials information, housing | Zinc die-casting |
| Materials information for bowl | Zinc die-casting |