



Data sheet

Part no.: **182967**

Page:1

FRM-M1-G1/4-Y

Branching module

| Feature | Data/description |
|------------------------------|--------------------------|
| Assembly position | Any |
| Operating pressure | ≥ 21 bar |
| Standard nominal flow rate | 2.800 l/min |
| Operating medium | Compressed air |
| Storage temperature | -10 - 80 °C |
| Medium temperature | -10 - 80 °C |
| Ambient temperature | -10 - 80 °C |
| Product weight | 128 g |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Contains PWIS substances |