



Data sheet

Part no.: **182968**

Page:1

FRM-M1-G1/4-Z

Branching module

Feature	Data/description
Assembly position	Any
Operating pressure	≥ 21 bar
Standard nominal flow rate	2.800 l/min
Operating medium	Compressed air
Storage temperature	-10 - 80 °C
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	128 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances