



Data sheet

Part no.: **182979**

Page:1

FRM-M3-G3/4-Y

Branching module

Feature	Data/description
Assembly position	Any
Operating pressure	≥ 21 bar
Standard nominal flow rate	21.000 l/min
Operating medium	Compressed air
Storage temperature	-10 - 80 °C
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	439 g
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 2	G3/4
Materials note	Contains PWIS substances