



## LD-M3-G1/2-ECO-2

### Diaphragm air dryer

| Feature                        | Data/description                                  |
|--------------------------------|---|
| Size                           | 3   |
| Series                         | M   |
| Assembly position              | Vertical +/- 5°                                   |
| Design structure               | Membrane dryer                                    |
| Inlet pressure 1               | 4 - 10 bar  |
| Standard nominal flow rate     | 100 l/min   |
| Atmospheric dew point          | -20 °C  |
| Operating medium               | Compressed air, filtered, unlubricated            |
| Pressure dew point             | -20 °C  |
| Storage temperature            | 5 - 50 °C   |
| Medium temperature             | 5 - 50 °C   |
| Ambient temperature            | 5 - 50 °C   |
| Product weight                 | 1.600 g   |
| Mounting type                  | Optional<br>Line installation<br>with accessories |
| Pneumatic connection, port 1   | G1/2  |
| Pneumatic connection, port 2   | G1/2  |
| Materials note                 | Contains PWIS substances                          |
| Materials information, housing | Zinc die-casting                                  |
| Materials information for bowl | Wrought Aluminium alloy                           |