



LD-M3-G1/2-ECO-4 Diaphragm air dryer

Feature	Data/description
Size	3
Series	M
Assembly position	Vertical +/- 5°
Design structure	Membrane dryer
Inlet pressure 1	4 - 10 bar
Standard nominal flow rate	300 l/min
Atmospheric dew point	-20 °C
Operating medium	Compressed air, filtered, unlubricated
Pressure dew point	-20 °C
Storage temperature	5 - 50 °C
Medium temperature	5 - 50 °C
Ambient temperature	5 - 50 °C
Product weight	2.400 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting
Materials information for bowl	Wrought Aluminium alloy