

Clamping module EV-63-5

Part number: 184859

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Clamping surface	Ø 63
Mounting position	optional
Mode of operation	Single-acting
Operating pressure	6 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% copper by mass are excluded from use. Exceptions are printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-10 °C...40 °C
Product weight	100 g
Type of mounting	With through-hole
Pneumatic connection	M3
Material housing	Die-cast aluminium
Material membrane	TPE-U(PU)