

Rod clevis CRSG-M27X2

Part number: 185361

FESTO



Data sheet

Feature	Value
Size	M27x2
Mounting position	optional
Based on standard	ISO 8140
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	2022.1 g
Note on materials	RoHS-compliant
Material bolt	High-alloy steel
Material clevis	High-alloy steel
Material nut	High-alloy steel
Material lock	High-alloy steel