


Adsorption dryer LDF-H2-N1/4-24

Part number: 185676

FESTO

For dry and clean compressed air.

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

Feature	Value
Assembly position	Vertical
Bowl guard	Metal bowl guard
Inlet pressure 1	4 ... 10.5 bar
Atmospheric dew point	-40 °C
Operating medium	Compressed air, filtered, unlubricated
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Corrosion resistance classification CRC	1
Medium temperature	2 ... 50 °C
Ambient temperature	2 ... 50 °C
Product weight	6,500 g
Mounting type	with through hole
Materials note	Free of copper and PTFE
Materials information, housing	Zinc die-casting