


# Pressure supply plate VIGP-03-4,0

Part number: 18654  
Product to be discontinued

FESTO

[For valve terminal](#)

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



## Data sheet

Feature	Value
Grid dimension	36 mm
Operating pressure	-0.9 ... 10 bar
Operating voltage range DC	24 V
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Product weight	400 g
Mounting method for sub-base	with internal (female) thread
Mounting method for valve	with through hole
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 5	G1/2