

# connecting cable KM12-M12-GSGD-2,5

Part number: 18684

FESTO



## Data sheet

Feature	Value
Operating voltage range AC	$\leq 60$ V
Operating voltage range DC	$\leq 75$ V
Permissible current load	3.8 A
Protection class	IP67
Ambient temperature with flexible cable installation	-5 ... 70 °C
Ambient temperature	-30 ... 70 °C
Electrical connection	Plug straight / socket straight M12x1 / M12x1 4-pin / 4-pin
Cable structure	4x0,25
Cable length	2.5 m
Cable sheath colour	Grey
Materials information, cable sheaths	PUR